

HI98129 • HI98130

pH/EC/TDS Testers

- **Waterproof**
 - Waterproof and designed to float
- **ATC**
 - Automatic Temperature Compensation
- **BEPS**
 - Alerts the user of low battery power that could adversely affect readings
- **HOLD feature**
 - HOLD button to freeze readings on the display
- **Two-point calibration**
 - Automatic one or two-point pH calibration

The HI98129 and HI98130 are waterproof testers that offer high accuracy pH, EC/TDS and temperature measurements in a single tester; no more switching between meters for your routine measurements. These floating, waterproof combination testers have an easy-to-read LCD and an automatic shut-off. pH and EC/TDS readings are automatically temperature-compensated.

These testers feature a replaceable pH electrode cartridge with an extendable cloth junction, as well as an EC/TDS graphite electrode. The renewable cloth junction provides an extended electrode life and the replaceable pH cartridge means that this tester does not need to be thrown away when the pH sensor is exhausted.

The EC/TDS conversion factor is user-selectable, as well as the temperature compensation coefficient (β).

Fast, efficient, accurate and portable, the Combo pH, EC/TDS and temperature testers combine all the features users have requested and more!



- **Replaceable pH electrode cartridge**
 - The Combo features an easy-to-replace pH electrode. The sturdy, snap-in connector means there are no pins to bend or break.



- **High accuracy EC/TDS graphite probe**
 - The graphite conductivity probe provides greater accuracy because it cannot be contaminated by salt deposits in the solution. The exposed temperature sensor provides fast response times and guarantees highly accurate temperature-compensated readings.



- **Extendable cloth junction**
 - Simply pull out 3 mm (1/8") and cut when the cloth junction becomes dirty to improve response time and stability.




LCD Display Features



- **On-screen battery life**
 - LCD indicates the percentage of battery power remaining upon startup.




- **HOLD function**
 - The HOLD function “freezes” the LCD display temporarily.




- **Instability & ATC indicators**
 - Ensures reliable EC and TDS measurements. ATC symbol is shown when active.



- **Standard or N.I.S.T buffer calibration**
 - Automatic calibration is performed with two sets of memorized buffers for greater accuracy.



- **Adjustable temperature coefficient factor**
 - Users can choose between different factors (β) for precise temperature compensated measurements.



- **Adjustable TDS conversion factor**
 - For measurement accuracy, users can choose between a range of conductivity to TDS conversion factors.

Specifications		HI98129	HI98130
pH	Range	0.00 to 14.00 pH	0.00 to 14.00 pH
	Resolution	0.01 pH	0.01 pH
	Accuracy	±0.05 pH	±0.05 pH
Conductivity	Range	0 to 3999 μ S/cm	0.00 to 20.00 mS/cm
	Resolution	1 μ S/cm	0.01 mS/cm
	Accuracy	±2% F.S.	±2% F.S.
TDS	Range	0 to 2000 mg/L (ppm)	0.00 to 10.00 g/L (ppt)
	Resolution	1 mg/L (ppm)	0.01 g/L (ppt)
	Accuracy	±2% F.S.	±2% F.S.
Temperature	Range	0.0 to 60.0°C / 32.0 to 140.0°F	0.0 to 60.0°C / 32.0 to 140.0°F
	Resolution	0.1°C / 0.1°F	0.1°C / 0.1°F
	Accuracy	±0.5°C / ±1°F	±0.5°C / ±1°F
Additional Specifications	EC/TDS Calibration	automatic, one point at 1413 μ S/cm or 1382 mg/L (ppm)	automatic, one point at 12.88 mS/cm or 6.44 g/L (ppt)
	pH Calibration	automatic, one or two-point with two sets of standard buffers (pH 4.01 / 7.01 / 10.01 or 4.01 / 6.86 / 9.18)	
	Temperature Compensation	pH: automatic; EC/TDS: automatic with β adjustable from 0.0 to 2.4% / °C	
	TDS Conversion Factor	0.45 to 1.00	
	pH Electrode	HI73127 (replaceable; included)	
	Environment	0 to 50°C (32 to 122°F); RH max 100%	
	Battery Type / Life	1.5V (4) / approx. 100 hours of continuous use; auto-off after 8 minutes of non-use	
Ordering Information	Dimensions / Weight	163 x 40 x 26 mm (6.4 x 1.6 x 1.0") / 100 g (3.5 oz.)	
		HI98129 (Combo) and HI98130 (Combo) are supplied with HI73127 pH electrode and HI73128 electrode removal tool, batteries and instructions.	

For a list of our pH calibration and electrode solutions, see section 3;
for EC and TDS solutions, see section 6



- **Calibrate directly in buffer solution sachets**
 - An easy calibration can be performed right in our buffer solution sachets for the most accurate readings.

HANNA
instruments